

B713

ELEGANCE AND PROTECTION

Bollé Safety offers a simple and flexible system, based on unique pricing. The Rx range is composed of a wide range of frames that can be glazed with 4 types of prescription lenses (single vision, bifocal, progressive and extended near) and 2 different lens materials (polycarbonate or trivex).



Size S: 38g | Size L: 40g

SUPPLIED WITH

Hard case,
microfibre cloth,
cord



FRAME

- Metal
- Acetate Temples
- Wire core Temples

LENS MATERIAL AVAILABLE

- Trivex
- Polycarbonate

Size S



Ref. B713S

Size L





Ref. B713L

- + ACETATE TEMPLES
- + BUILT-IN SIDE SHIELDS
- + NON-SLIP NOSE PADS
- + WIRE CORE TEMPLES

bollé
SAFETY

B713



ELEGANCE AND PROTECTION

MODEL	VERSIONS	REF.	SIZE	LENS HEIGHT	LENS MARKING	TEMPLE LENGTH
B713	S - Light grey side shields	B713S	52/16	35 mm	 RIO (for clear outdoor)	130 mm
	L - Light grey side shields	B713L	54/17	35 mm	 RI (for tinted outdoor)	130 mm

LENS MARKING

- R.** The letter 'R' signifies prescription eye protectors.
- I.** The letter 'I' signifies 'Medium Impact' approval.
- O.** The letter 'O' marking signifies that the product has been approved for the use both outdoors and indoors and the terminology used by Australian standards is 'outdoor untinted'. This marking appears on all clear, amber and contrast lenses.

OCULAR LENS CATEGORY:

-  **RIO** for clear outdoor
-  **RI** for tinted outdoor

FRAME MARKING

AS/NZS 1337: tested and approved to Australian Standards – Prescription Eye Protectors against Low and Medium Impact.

CLEANING AND STORAGE

CLEANING : The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE : Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged, also replace the complete product. After each use it is recommended to keep the spectacles in a rigid case.

STORAGE : All products must be stored in a dry and clean environment.

STANDARD ASSEMBLY RESTRICTIONS:

Maximum sphere power: +6.00/-6.00

Maximum cylinder compared with sphere: -3.00

CORRECTED BASE:

Corrected base: 4 (size S) / 4 (size L)

CHARACTERISTICS	
LENS	Trivex, Polycarbonate
TYPES OF CORRECTIONS AVAILABLE	Single vision, Bifocal, Progressive, Extended near, Transitions, Polarised, AR coating, Blue shield
FRAME	Metal / Chocolate
STRAP	Non applicable
FOAM	Non applicable

20/04/2019

Bollé Safety APAC
Bollé Safety AU Pty Limited
32-40 Fairchild Street
Heatherton VIC 3202
T: 1300 138 098
E: rxsfatyau@bolle-safety.com

bollesafety.com.au

New Zealand
T.: 0800 2655 369
E: rxsfatyau@bolle-safety.com

bolle
SAFETY